


NOTES:

- 1. SUBSTRATE: XP42-200 ON PMMA
- 2. WAVELENGTH RANGE (nm): 400 - 700
- 3. EXTINCTION RATIO: 9000:1
- 4. OPERATING TEMPERATURE (°C): -40 to +80
- 5. TRANSMISSION (%):
SINGLE: 42
PARALLEL: 36
CROSSED: <0.004
- 6. RoHS: COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]

THE POLARIZERS CONSISTS OF A POLYMER POLARIZATION
FILM LAMINATED ONTO PMMA.

THIRD ANGLE PROJECTION		TITLE		600 x 450mm LINEAR PLASTIC POLARIZER (XP42-200)	
ALL DIMS IN	mm	DWG NO	14341	SHEET 1 OF 1	