


PN: MS-385-I-Y-A



## INPUT PARAMETER

Wavelength [nm]:	1064
Beam Mode (SM/MM):	SM or MM
Minimum Beam Diameter [mm]:	>0.48

## ELEMENT PARAMETER

Element Type:	Window
Material:	Fused Silica
Element Size [mm]:	25.4
Clear Aperture [mm]:	22.9
Thickness [mm]:	3
Coating:	AR/AR coating

## OUTPUT PARAMETER

Number of Spots:	6
Separation Angle [deg]:	0.76
$\theta_f$ [deg]:	3.80
Transmission efficiency:	Close to 100%
Overall Efficiency:	~ 82%
Uniformity (Contrast) [%]:	<5%
Zero-Order relative to the incident beam [%]:	<1.5

**Holo/Or can improve the performances of this item. Please send us your requirements**