

NOTES:



- SUBSTRATE:  
S-LAH64
- CENTERING TOLERANCE (AT 587.6nm):  
BEAM DEVIATION (HALF ANGLE): <3 arcmin
- COATING (APPLY ACROSS COATING APERTURE)  
S1: NIR (600-1050nm)  
Ravg < 0.5% @ 600 - 1050nm @ ±30° AOI  
Rabs < 1.5% @ 600 - 1050nm @ ±30° AOI  
S2: NIR (600-1050nm)  
Ravg < 0.5% @ 600 - 1050nm @ ±30° AOI  
Rabs < 1.5% @ 600 - 1050nm @ ±30° AOI

4. EDGES: FINE GROUND

5. ASPHERIC FIGURE ERROR: 0.75 μm RMS

6. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE):



$$Z_{ASPH}(Y) = \frac{(1/RADIUS)^2 * Y^2}{1 + \sqrt{1 - (1+k) * (1/RADIUS)^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$



SECTION A-A

COEFFICIENT TABLE 6.

COEFFICIENT	S1
SEMI-DIAMETER	7.500000E+00
(1/RADIUS)	1.07296137E-01
k	-8.830000E+00
D	0.000000E+00
E	3.953300E-05
F	-3.748800E-08
G	-6.650300E-10
H	-2.770000E-12
J	1.808000E-14
L	0.000000E+00

	S1	S2	 Edmund Optics®			
SHAPE	CONVEX	PLANO	BFL @ 780nm: 9.02			
RADIUS	9.320	INFINITY				
SURFACE QUALITY	40-20	40-20				
CLEAR APERTURE	13.5 mm	13.5 mm	TITLE 15mm Dia., 0.63 NA, 600-1050nm Coated, NIR Aspheric Lens			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN mm	DWG NO 16281	SHEET 1 OF 1	