

NOTES:



1. SUBSTRATE: N-BK7
2. CENTERING TOLERANCE:
BEAM DEVIATION (HALF ANGLE): < 3 arcmin
3. COATING (APPLY ACROSS CLEAR APERTURE)

S1:NONE
S2:NONE

4. EDGES: FINE GROUND



5. ASPHERIC FIGURE ERROR: 0.75 μ m RMS

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

		EFL @ 780nm: 100.00		 Edmund Optics®		
SHAPE	S1 CONVEX	S2 PLANO				
SURFACE QUALITY	40-20	40-20		TITLE	100mm Dia., 0.50 NA, Uncoated, NIR Aspheric Lens	
CLEAR APERTURE (mm)	Ø 92.00	Ø 92.00		DWG NO	13510	SHEET 1 OF 1
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN mm			