

NOTES:


- 1. SUBSTRATE: FUSED SILICA (CORNING 7980)
- 2. S2 TO BE PARALLEL WITH S1 TO WITHIN <1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(AVG) ≤0.4% @ 425 - 675nm

4. FINE GRIND SURFACE

5. ROHS COMPLIANT







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

| | \$1 | \$2 |
|---------------------|----------------------|----------------------|
| SHAPE | PLANO | PLANO |
| SURFACE QUALITY | 40-20 | 40-20 |
| CLEAR APERTURE (mm) | Ø18.00 | Ø18.00 |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |

| THIRD ANGLE PROJECTION | ϕ | TITLE |
|------------------------|--------|-------|
| ALL DIMS IN | mm | DWG N |

| Edmund Optic | S® |
|--|--------|
| 20mm Dia., 2mm Thick, VIS 0° Coated Fused Silica Window | ί, λ/4 |

AS IN mm DWG NO 18326 SHEET 1 OF 1