



NOTES:


1. MATERIAL: PMMA
2. COATING (APPLY ACROSS CLEAR APERTURE):  
R(AVG) < 0.5% @ 700 - 1100nm
3. FOCAL LENGTH TOLERANCE: ±%1
4. RoHS: COMPLIANT



SECTION A-A

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

		EFL: 102.00mm		 <b>Edmund Optics®</b>			
		BFL: 98.00mm					
				TITLE			
				25.4mm DIA. f/4 NIR COATED, MOLDED ACRYLIC ASPHERIC LENS			
SHAPE	S1 CONVEX	S2 PLANO	ALL DIMS IN	mm	DWG NO	64588	SHEET 1 OF 1
BEVEL MAX FACE	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					