NOTES:

1. SUBSTRATE: POLYMER FILM XP44-40

2. OPERATING TEMPERATURE: -40 TO +80 °C


3. WAVELENGTH RANGE: 400 - 700 nm

4. EXTINCTION RATIO: 2000:1

5. POLARIZATION EFFICIENCY (%): >99.95

6. TRANSMISSION (%):
   SINGLE: 44.2 ±1.5
   PARALLEL: 38.6
   CROSSED: <0.02

7. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY:
DO NOT MANUFACTURE PARTS TO THIS DRAWING

Edmund Optics®

THIRD ANGLE PROJECTION		TITLE	200 x 200mm High Transmission Linear Polarizing Film (XP44-40)
ALL DIMS IN	mm	DWG NO	19022
			SHEET 1 OF 1