



NOTES:

1. SUBSTRATE:  
VACUUM UV GRADE CaF<sub>2</sub>
2. SURFACE S2 TO BE PARALLEL WITH S1 TO <1 arcmin
3. COATING (APPLY ACROSS CLEAR APERTURE)  
S1 & S2: R(AVG) < 1% FROM 1650-3000nm @ 0° AOI  
R(ABS) < 2% FROM 1650-3000nm @ 0° AOI



4. FINE GRIND SURFACE



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	Ø4.50	Ø4.50
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



ALL DIMS IN

mm

**EO**® **Edmund Optics**®

TITLE

Ø5mm, BBAR (1650-3000nm), CALCIUM  
FLUORIDE WINDOW

DWG NO

15962

SHEET  
1 OF 1