

NOTES:

1. SUBSTRATE: N-SF6

2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: VIS-EXT+ (350-700nm)

R(AVG) <0.5% @ 350 - 700nm @ ±30° AOI

R(ABS) <1.5% @ 350 - 700nm @ ±30° AOI



3. EDGES: FINE GROUND

4. CENTERING: <3 ARCMIN

5. ASPHERE FIGURE ERROR: 0.25µm RMS

6. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE)

$$Z_{ASPH}(Y) = \frac{(1/RADIUS)^2 * Y^2}{1 + \sqrt{1 - (1+k) * (1/RADIUS)^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$




SECTION A-A

COEFFICIENT TABLE 6.

COEFFICIENT	S1
SEMI-DIAMETER	1.000000E+01
(1/RADIUS)	0.082795165
k	-0.6243706
D	0.0000000E+00
E	2.5625580E-06
F	-2.3980870E-08
G	-2.9296510E-10
H	0.0000000E+00
J	0.0000000E+00
L	0.0000000E+00

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 587.6nm	15	 Edmund Optics®		
SHAPE	CONVEX	PLANO	BFL @ 587.6nm	9.24			
RADIUS	12.078	INFINITY			TITLE	25mm Dia., 0.83 Numerical Aperture, 350-700nm Coated, Precision Aspheric Lens	
SURFACE QUALITY	40-20	40-20					
CLEAR APERTURE	Ø22.5	Ø22.5	ALL DIMS IN mm		DWG NO	16962	
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					
						SHEET 1 OF 1	

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**