NOTES:


- 1. SUBSTRATE MATERIAL: FLOAT GLASS
- 2. COATING (APPLOW ACROSS CLEAR APERTURE): \$1: ALUMINUM


S2: NONE


3. BLAZE ANGLE: 22° 0' NOMINAL BLAZE WAVELENGTH: 10000nm GROOVE DENSITY: 75 GROOVES/mm



5. Rohs Compliant







FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

| | E | Edr | าเ | ın | d | Op | otics® |
|--|---|-----|----|----|---|----|--------|
| | | | | | | | |

| | | | | 4 - | | Richardson Graings 75 Grooves, 25 x | |
|----------------|-------------|-------------|------------------------|-----|--------|--|-----------------|
| | \$1 | \$2 | THIRD ANGLE PROJECTION | | TITLE | 25mm, 10µm, Plane Ruled Reflection Grating | |
| SHAPE | PLANO | PLANO | |]! | | | CUEET |
| CLEAR APERTURE | 22.5 x 22.5 | 22.5 x 22.5 | ALL DIMS IN | mm | DWG NO | 15770 | SHEET 1 OF 1 |