

NOTES:

1. SUBSTRATE: N-SF5

2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: SWIR+ (900-1700nm)

R(AVG) <0.5% @ 900 - 1700nm @ ±30° AOI

R(ABS) <1% @ 900 - 1700nm @ ±30° AOI



3. EDGES: FINE GROUND

4. CENTERING: <3 ARCMIN

5. ASPHERE FIGURE ERROR: 0.25μm RMS

6. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE)

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS})^2 Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$





SECTION A-A

COEFFICIENT TABLE 6.

COEFFICIENT	S1
SEMI-DIAMETER	2.000000E+01
(1/RADIUS)	4.954910E-02
k	-1.819186E+00
D	0.000000E+00
E	1.952657E-05
F	-9.527297E-09
G	1.162971E-11
H	-1.020802E-14
J	1.221727E-18
L	0.000000E+00

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 587.6nm	30.00	 Edmund Optics®		
SHAPE	CONVEX	PLANO	BFL @ 587.6nm	18.04			
RADIUS	20.182	INFINITY			40mm Dia., 0.66 Numerical Aperture, 900-1700nm Coated, Precision Aspheric Lens		
SURFACE QUALITY	40-20	40-20					
CLEAR APERTURE	Ø36.00	Ø36.00			17009		
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					
			ALL DIMS IN	mm	DWG NO		
						SHEET 1 OF 1	