



NOTES:

- 1. SUBSTRATE:
D-ZLAF52LA
- 2. NUMERICAL APERTURE: 0.50
- 3. COATING
S1 & S2: R(ABS) <1.0% @1050 - 1600nm
- 4. FOCAL LENGTH TOLERANCE: ±1%
- 5. TRANSMITTED WAVEFRONT ERROR (λ, RMS @ 632.8NM): <0.150
- 6. DESIGN WAVELENGTH: 1550nm



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	1.05	 Edmund Optics®		
			WD	0.61			
SHAPE	CONVEX	CONVEX			TITLE	LightPath 355198 1.4mm Dia., 0.50 NA, BBAR (1050-1600nm), Molded Aspheric Lens	
SURFACE QUALITY	40-20	40-20					
CLEAR APERTURE	Ø 1.10	Ø 0.84	ALL DIMS IN	mm	DWG NO	16704	SHEET 1 OF 1
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					