

NOTES:

1. SUBSTRATE: N-SF6

2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: NIR+ (600-1050nm)

R(AVG) <0.5% @ 600 - 1050nm @ ±30° AOI
R(ABS) <1.5% @ 600 - 1050nm @ ±30° AOI



3. EDGES: FINE GROUND

4. CENTERING: <3 ARCMIN

5. ASPHERE FIGURE ERROR: 0.25µm RMS

6. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE)

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS}) * Y^2}{1 + \sqrt{1 - (1 + k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$




SECTION A-A

COEFFICIENT TABLE 6.

COEFFICIENT	S1
SEMI-DIAMETER	1.000000E+01
(1/RADIUS)	4.967710E-02
k	-8.641265E-01
D	0.000000E+00
E	3.151369E-06
F	-1.837155E-09
G	-3.336790E-12
H	0.000000E+00
J	0.000000E+00
L	0.000000E+00

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 587.6nm	25	 Edmund Optics®		
SHAPE	CONVEX	PLANO	BFL @ 587.6nm	19.54			
RADIUS	20.130	INFINITY	THIRD ANGLE PROJECTION 		25mm Dia., 0.50 Numerical Aperture, 600-1050nm Coated, Inked, High Precision Aspheric Lens		
SURFACE QUALITY	40-20	40-20					
CLEAR APERTURE	Ø22.5	Ø22.5	ALL DIMS IN mm		DWG NO 16980INK		
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					
					SHEET 1 OF 1		

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**