NOTES:

1. SUBSTRATE MATERIAL: Fused Silica (Corning 7980)

2. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: Rabs ≤1.0% @ 350 - 450nm Rayg ≤1.5% @ 250 - 700nm




ARROW POINTS TOWARDS TILTED SURFACE



FINE GROUND SURFACE

5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

6. Rohs Compliant



SECTION A-A

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2
SHAPE	PLANO	PLANO
RADIUS	∞	8
MIN CLEAR APERTURE	Ø11.25	Ø11.25
SURFACE QUALITY	20-10	20-10
SURFACE ACCURACY	λ/10	λ/10
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

	Edmund Optics®					
	THIRD ANGLE PROJECTION		TITLE	12.5mm Dia., UV-VIS Coated, Fused Silica Wedged Window		
)	ALL DIMS IN	mm	DWG NO	17663	SHEET 1 OF 1	