



NOTES:

1. SUBSTRATE: N-SF5
2. COATING (APPLY ACROSS CLEAR APERTURE)
S1: NONE
S2: NONE
3. EDGES: FINE GROUND
4. CENTERING: <3 ARCMIN
5. ASPHERE FIGURE ERROR: 0.25µm RMS

6. BLACKENED SURFACE

7. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE)

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS})^2 * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$



SECTION A-A

COEFFICIENT TABLE 6.

COEFFICIENT	S1
SEMI-DIAMETER	1.500000E+01
(1/RADIUS)	6.606765E-02
k	-1.081599E+00
D	0.000000E+00
E	1.9847737E-05
F	8.487952E-09
G	6.836397E-12
H	-5.198550E-14
J	0.000000E+00
L	0.000000E+00

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 587.6nm	22.50	 Edmund Optics®		
SHAPE	CONVEX	PLANO	BFL @ 587.6nm	13.53			
RADIUS	15.136	INFINITY	THIRD ANGLE PROJECTION		TITLE	30mm DIA., 0.66 NUMERICAL APERTURE, UNCOATED, INKED, HIGH PRECISION ASPHERIC LENS	
SURFACE QUALITY	40-20	40-20			DWG NO	37433INK	
CLEAR APERTURE	Ø27.00	Ø27.00					
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm			SHEET 1 OF 1