


NOTES:


- 1. SUBSTRATE: POLYMER FILM XP42-70
- 2. OPERATING TEMPERATURE (°C): -10 to +60
- 3. OPERATING HUMIDITY (%): ≤80 (No Condensation)
- 4. WAVELENGTH RANGE: 400-700nm
- 5. POLARIZATION: >99.98
- 6. TRANSMISSION (%):
SINGLE 42 ±2
PARALLEL: 36.4
CROSSED: <0.004
- 7. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	600 x 900mm Dia. Linear Polarizer (XP42-70)	
ALL DIMS IN	mm	DWG NO	19950	SHEET 1 OF 1