




FOCAL LENGTH (EFL): 35 ±0,35
BACK FOCAL LENGTH (BFL): 33,85

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	31,566±0,032 CX	GLASS FUSED SILICA 458/678	R	31,566±0,032 CX
Øe	11		Øe	11
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-


PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

λ = 587,6nm

FIRST ANGLE
PROJECTION



Edmund Optics®

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm

TITLE

12mm Dia, x 35mm FL, Uncoated, UV
Double-Convex Lens

DWG NO

48037

SHEET SIZE
A4

SHEET
1 OF 1