


NOTES:

1. SUBSTRATE:  
Calcium Fluoride, IR Grade (CaF<sub>2</sub>)
2. CENTERING TOLERANCE: <3 ARCMIN
3. COATING (APPLY ACROSS CLEAR APERTURE)  
  
S1&S2: NONE
4. FINE GRIND SURFACE
5. FOCAL LENGTH TOLERANCE: ±2%
6. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 5µm	500	 <b>Edmund Optics®</b>		
SHAPE	CONVEX	CONVEX	BFL @ 5µm	497.72			
RADIUS	398.1	398.1			TITLE	76.2mm Dia. x 500mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF <sub>2</sub> ) DCX Lens	
IRREGULARITY AT 632.8nm	λ	λ					
SURFACE QUALITY	60-40	60-40	ALL DIMS IN		DWG NO	24777	
CLEAR APERTURE	ø68.58	ø68.58					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	mm				SHEET 20 OF 20