



NOTES:

1. SUBSTRATE:  
H-K51
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: MgF2 (400-700nm)  
R(AVG) ≤ 1.75% @ 400 - 700nm


3. CENTERING: ≤30 ARCMIN



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

|                 |                     |                     |  |       |   |   |                 |
|-----------------|---------------------|---------------------|--|-------|---|---|-----------------|
|                 | S1                  | S2                  | EFL @ 587.6nm  | 32.00 |  <b>Edmund Optics®</b> | TITLE<br>50.8mm Dia. x 32mm FL, MgF2 Coated,<br>Aspheric Condenser Lens |                 |
| SHAPE           | CONVEX              | CONVEX              | BFL @ 587.6nm  | 17    |   |   |                 |
| SURFACE QUALITY | 80-50 (typical)     | 80-50 (typical)     | THIRD ANGLE PROJECTION  |       | DWG NO<br>21203   |   | SHEET<br>1 OF 1 |
| CLEAR APERTURE  | ∅ 45.72             | ∅ 45.72             |  |       |   |   |                 |
| BEVEL           | PROTECTED AS NEEDED | PROTECTED AS NEEDED | ALL DIMS IN  | mm    |   |   |                 |