

NOTES:

1. SUBSTRATE:
N-BK7

2. BEAM DEVIATION: ≤ 2 ARCMIN



3. COATING (APPLY ACROSS CLEAR APERTURE):
VIS (430-670nm)
S2, S3, S4: $R_{avg} < 0.5\%$ @ 430 - 670nm
S5: MULTILAYER DIELECTRIC TO ACHIEVE:
TRANSMISSION $> 45\% \pm 10\%$
POLARIZATION $< 6\%$

4. ELEMENTS CEMENTED WITH NORLAND OPTICAL
ADHESIVE NOA 61

5. ABSORPTIVE SURFACE TREATMENT, INCLUDING BEVEL

6. DIMENSIONS APPLY AFTER SURFACE TREATMENT

7. MARK IDENTIFIES BEAMSPLITTER COATED RIGHT ANGLE
PRISM



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S2, S3, S4
SHAPE	PLANO
SURFACE FLATNESS	$\lambda/8$
SURFACE QUALITY	40 - 20
CLEAR APERTURE	$> 90\%$
BEVEL	PROTECTED AS NEEDED

		Edmund Optics	
		TITLE 15mm VIS, 50R/50T, Non-Polarizing In-Line Cube Beamsplitter	
ALL DIMS IN mm	DWG NO 20095	SHEET 2 OF 5	