






f' : 50,808 $\pm$ 0,51

BACK FOCAL LENGTH (BFL): 44,084



LEFT SURFACE			MATERIAL	RIGHT SURFACE				
R 39,87 CX Øe 49,3 λ AR R(750nm - 800nm, 0°) ≤ 1,50% R(800nm - 1550nm, 0°) ≤ 1,00% Rave(750nm - 1550nm, 0°) ≤ 0,70% 3/ 3 (0,5) λ=632,8 nm 4/ 1,27' 5/ 40 - 20 6/ - P			GLASS N-SF11 785/258 Nd: 1,785 Vd: 25,68	R ∞ PL Øe 49,3 λ AR R(750nm - 800nm, 0°) ≤ 1,50% R(800nm - 1550nm, 0°) ≤ 1,00% Rave(750nm - 1550nm, 0°) ≤ 0,70% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - P				
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 587,6nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110				FIRST ANGLE PROJECTION  ALL DIMS IN: mm			ED [®] Edmund Optics [®] TITLE 50,8mm Dia x 50,8079mm FL, NIR II Coated, Plano-Convex Lens DWG NO 71338 SHEET SIZE A4 SHEET 1 OF 1	