





f' : 50,808 $\pm$ 0,51

BACK FOCAL LENGTH (BFL): 44,084



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 39,87 CX			GLASS N-SF11 785/258 Nd: 1,785 Vd: 25,68	R ∞ PL		
Øe 49,3				Øe 49,3		
λ AR R(880nm, 0°) ≤ 0,25% Rave(400nm - 870nm, 0°) ≤ 1,25% Rave(890nm - 1000nm, 0°) ≤ 1,25%				λ AR R(880nm, 0°) ≤ 0,25% Rave(400nm - 870nm, 0°) ≤ 1,25% Rave(890nm - 1000nm, 0°) ≤ 1,25%		
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm		
4/ 1,27'				4/ -		
5/ 40 - 20				5/ 40 - 20		
6/ -				6/ -		
P				P		
PROTECTIVE CHAMFERS AS NEEDED			® Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE 50,8mm Dia x 50,8079mm FL, VIS-NIR Coated, Plano-Convex Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO 71340	
					SHEET SIZE A4	SHEET 1 OF 1