


- NOTES:
- 1. SUBSTRATE:
FUSED SILICA
 - 2. RoHS: COMPLIANT
 - 3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN < 5 ARCMIN
 - 4. COATING (APPLY ACROSS CLEAR APERTURE)
- S1 & S2: UV-AR (250-425nm)
Rabs ≤1.0% @ 250 - 425nm Ravg ≤0.75% @ 250 - 425nm Ravg ≤0.5% @ 370 - 420nm



5. FINE GRIND SURFACE



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE ACCURACY	1λ	1λ
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	Ø 13.5	Ø 13.5
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	15mm Dia. 1mm Thick UV-AR Coated, 1λ Fused Silica Window
ALL DIMS IN	mm	DWG NO	23309
			SHEET 9 OF 35