


[All Products](#) / [Optics](#) / [Polarization Optics](#) / [Linear Polarizers](#) / [Wire Grid \(Reflective\) Polarizers](#)

Ultra Broadband Wire Grid Polarizers



- Reflect S-Polarized Light
- Transmit P-Polarized Light
- Excellent Performance from UV to IR

Common Specifications

Physical & Mechanical Properties

Dimensional Tolerance (mm):	±0.4	Construction:	Wire Grid
Alignment Tolerance (°):	±1.0		

Optical Properties

Angle of Incidence (°):	±20 without depolarization		
Extinction Ratio:	5000:1 @ 3200nm	Substrate:	Fused Silica (Corning 7980)
Surface Quality:	80-50	Transmission (%):	>80 (Typical) @ 450nm
Wavelength Range (nm):	300 - 3200		

Material Properties


Thermal Expansion:	5.5 x 10 ⁻⁷ /°C
--------------------	----------------------------

Environmental & Durability Factors

Operating Temperature (°C):	-40 to +200
-----------------------------	-------------

Technical Information

The reference mark on the side of the polarizer indicates the transmission axis as shown:



Products

Alignment Tolerance (°)	Operating Temperature (°C)	Substrate	Thickness (mm)	CA (mm)	Dimensions (mm)	Stock Number	Price	Buy
±1.0	-40 to +200	Fused Silica	5.80	8.5	-	#34-314	₹86,803 Qty 11+ ₹73,335	10 to 12 days
±1.0	-40 to +200	Fused Silica	2.13	8.5 x 8.5	12.5 x 12.5	#68-749	₹75,125 Qty 11+ ₹64,071	Contact Us
±1.0	-40 to +200	Fused Silica	5.80	19.0	-	#34-315	₹1,07,433 Qty 11+ ₹92,330	10 to 12 days
±1.0	-40 to +200	Fused Silica	2.13	21.0 x 21.0	25.0 x 25.0	#68-750	₹94,977 Qty 11+ ₹82,210	10 to 12 days
±1.0	-40 to +200	Fused Silica	5.80	42.0	-	#34-316	₹2,12,141 Qty 11+ ₹1,82,091	10 to 12 days
±1.0	-40 to +200	Fused Silica	2.13	46.0 x 46.0	50.0 x 50.0	#68-751	₹1,70,881 Qty 11+ ₹1,45,112	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
Phone: 1-800-363-1992 : www.edmundoptics.com