


[All Products](#) /
 [Optics](#) /
 [Optical Lenses](#) /
 [Cylinder Lenses](#) /
 [Specialty Lenses](#)

Slow Axis Collimators



- Designed for Use with Laser Bars
- Can be Used With [Fast Axis Collimators](#)
- Low Curvature Deviation for Increased Collimation
- [Fast Axis Collimators](#) Also Available

Common Specifications


Physical & Mechanical Properties

Clear Aperture CA (mm):	11.0 x 1.4	Height (mm):	1.50
Height Tolerance (mm):	0.05	Length (mm):	12.00
Length Tolerance (mm):	±0.05		

Optical Properties

Substrate:	S-TiH53		
Coating:	BBAR (790-990nm)	Wavelength Range (nm):	790 - 990
Coating Specification:	$R_{avg} < 1.0\%$ @ 790 - 990nm	Pitch (μm):	500.00
Surface Accuracy:	$\lambda/4$	Transmission (%):	>99

Technical Information



Products

Length (mm)	EFL (mm)	Substrate	Coating	Stock Number	Price	Buy
12.00	4.25	S-TIH53	BBAR (790-990nm)	#88-403	₹14,869 Qty 11+ ₹13,390	10 to 12 days
12.00	2.88	S-TIH53	BBAR (790-990nm)	#88-404	₹14,869 Qty 11+ ₹13,390	10 to 12 days
12.00	1.81	S-TIH53	BBAR (790-990nm)	#88-405	₹14,869 Qty 11+ ₹13,390	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com