

[All Products](#) / [Optics](#) / [Polarization Optics](#) / [Retarders \(Waveplates\)](#) / [Polarization Rotators and Converters](#)

Radial Polarization Converters



- Converts Linear Polarization to Radial or Azimuthal
- Converts Circular Polarization to an Optical Vortex (Donut-Shaped Beam)
- High Damage Thresholds in the Nano- and Femtosecond Range
- Higher-Order Versions Can Generate Higher Order Polarization Patterns and Optical Vortices

Common Specifications


Physical & Mechanical Properties

Clear Aperture CA (mm):	6.0	Diameter (mm):	25.40
Thickness (mm):	3.00 ±0.1	Dimensional Tolerance (mm):	+0.0/-0.1
Construction:	Self-Organized Nanogratings		

Optical Properties

Substrate:	Fused Silica (Corning 7980)		
Surface Quality:	20-10	Transmission (%):	80-94 (wavelength dependent)
Surface Flatness (P-V):	$\lambda/8$	Damage Threshold, By Design:	20 J/cm ² @ 1064nm, 3.5ns

Technical Information



Products

Wavelength Range (nm)	DWL (nm)	CA (mm)	Dia. (mm)	Type	Surface Quality	Stock Number	Price	Buy
612 - 652	632	6.0	25.40	Polarization Converter	20-10	#89-447	₹3,43,319	Contact Us
775 - 825	800	6.0	25.40	Polarization Converter	20-10	#89-448	₹3,43,319	Contact Us
995 - 1065	1030	6.0	25.40	Polarization Converter	20-10	#89-449	₹3,43,319	Contact Us



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com