


NOTES:

- 1. SUBSTRATE MATERIAL: FUSED SILICA
- 2. ONLY ROHS-COMPLIANT MATERIALS ARE ACCEPTABLE.
DO NOT SUBSTITUTE WITH ROHS EXEMPT OR NON-COMPLIANT MATERIALS
- 3. COATING (APPLY ACROSS CLEAR APERTURE)
S1 & S2 : UNCOATED



4. FINE GRIND SURFACE

- 5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
- 6. CHIPS OUTSIDE OF CLEAR APERTURE: <0.5
- 7. CLEAR APERTURE AND COATING APERTURE ARE CENTERED ON SURFACES



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1 & S2				
SHAPE	PLANO				
SURFACE QUALITY	20-10				
SURFACE FLATNESS	λ/10	TITLE 25mm Dia., Uncoated, 4° Fused Silica Wedged Window			
CLEAR APERTURE	Ø22.50				
BEVEL	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO 25670	SHEET 1 OF 1