

[All Products](#) / [Laser Optics](#) / [Laser Beamsplitters](#)

TECHSPEC® Laser Line Polarizing Plate Beamsplitters



- 45° Angle of Incidence
- Reflects S-Polarized Light, Transmits P-Polarized Light
- Available for Nd:YAG Harmonics and HeNe Wavelengths

Common Specifications

Physical & Mechanical Properties

Clear Aperture (%):	90	Construction:	Thin Film Dielectric
Dimensional Tolerance (mm):	+0.00/-0.25	Thickness (mm):	6.00 ±0.25
Optical Properties			
Angle of Incidence (°):	45±2	Extinction Ratio:	10,000:1
P-Polarization Transmission (%):	>98	S-Polarization Reflection (%):	>99
Substrate:	Fused Silica	Surface Quality:	40-20
Transmitted Wavefront, P-V:	$\lambda/4$ @ 633nm	Damage Threshold, By Design:	2 J/cm ² @ 532nm, 10ns, S or P Polarization

Technical Information

Products

Dia. (mm)	DWL (nm)	Stock Number	Price	Buy
25.00	355	#21-884	₹44,460 Qty 6+ ₹38,880	10 to 12 days
25.00	532	#21-887	₹44,460 Qty 6+ ₹38,880	10 to 12 days
25.00	633	#21-890	₹44,460 Qty 6+ ₹38,880	10 to 12 days
#21-891 Clearance				
				
50.00	633	Clearance	₹50,108	10 to 12 days
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.				
25.00	1064	#21-893	₹44,460 Qty 6+ ₹38,880	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
 Phone: 1-800-363-1992 :
www.edmundoptics.com