





FOCAL LENGTH (EFL): $7 \pm 0,07$
 BACK FOCAL LENGTH (BFL): 5,5

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R 5,5 CX Øe 6,3 (λ) - 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -		GLASS N-SF11 785/258 Nd: 1,785 Vd: 25,68	R ∞ PL Øe 6,3 (λ) - 3/ 3 (0,5) λ=632,8 nm 4/ 3,82' 5/ 40 - 20 6/ -	
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 587,6nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110		FIRST ANGLE PROJECTION  ALL DIMS IN: mm	 Edmund Optics® TITLE 7mm Dia x 7mm FL, Uncoated, Plano-Convex Lens DWG NO 28946 SHEET SIZE A4 SHEET 1 OF 1	