


# Datasheet - characterization

Trace Code\*: **BioPixS0068**

Model	OCTTP01
Features	USAF Group 2 to 8, point spread function (PSF), annotated Ronchi ruling (10, 100 lines/mm), alignment markers
Feature depth	0.5 mm
Substrate	BioPixS Phantom
Phantom optical properties	Absorption = $0.22 \text{ cm}^{-1}$ , Reduced scattering = $12.3 \text{ cm}^{-1}$ @780 nm
Overall phantom dimension	21x21x3 mm
Batch code	OCTTP01-P-CC1B1za
Refractive index (RI)	1.5
Surface finish^	Polished
Application	Lateral resolution, distortion, calibration, alignment, reference



Batch test image:



OCT test system specifications: Spectral Domain OCT Imaging System, 1300 nm, axial resolution is 5.5 microns, lateral resolution of 13 microns.

\*Cite/Reference Trace code in your publications to make your research traceable. This will help the peer community to trace the phantoms used in your research.

^for matte finish visit <https://biopixstandards.com/products/oct-test-targets-and-phantoms/>


## BioPixS Limited

3 Monastery Mews, Blarney Street  
Gurranabraher T23 HW11 Cork, Ireland

<https://biopixstandards.com/>  
VAT Reg. No: 3689183LH

# Datasheet - characterization

Phantom image:



Feature details:

