

TECHSPEC® 0.15X - 0.5X VariMagTL™ Non-Telecentric Lens



0.15X - 0.5X VariMagTL™ Non-Telecentric Lens, #87-536

Stock **#87-536** 10 TO 12 DAYS



1



₹45,240.00

ADD TO CART

Qty 1+

₹45,240.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Iris Option:
Variable

Length (mm):
59.20

Filter Thread:
M25.5 x 0.50 (Female)

Maximum Diameter (mm):
32

Resolution:
75 lp/mm @ >20%

Weight (g): 101
Maximum Rear Protrusion (mm): 1.92
Maximum Image Circle (mm): 11.00
Numerical Aperture NA, Object Side: 0.0587
Number of Elements (Groups): 5 (4)
Typical Distortion @ 588nm (%): <0.1
Type: Variable Magnification Lens
Primary Magnification PMAG: 0.15X - 0.5X
Maximum Sensor Format: 2/3"
Working Distance (mm): 50 - 179.8
Mount: C-Mount
Style: Non-Telecentric, Variable Magnification
Aperture (f/#): f/2.8 - f/22
Coating Specification: λ/4 MgF ₂ @ 550nm
Entrance Pupil Position (mm): 30.1
Object Space Principal Plane (mm): 28.92
Image Space Principal Plane (mm): -16.17
Field of View at Max Sensor Format: Horizontal: 61.6 - 17.6mm - 15.8° Vertical: 61.6 - 13.2mm - 11.8° Diagonal: 46.9 - 22.0mm - 19.8°
Maximum Distortion (%): 0.05
FOV @ Max Sensor Format, H x V (mm): 58.7 x 44.0 - 17.6 x 13.2
Exit Pupil Position (mm): -15.04
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View