

[All Products](#) /
 [Optics](#) /
 [Polarization Optics](#) /
 [Linear Polarizers](#) /
 [Absorptive \(Dichroic\) Polarizers](#) /
 [Laminated Film Polarizers](#)

NIR Glass Linear Polarizers



- Ideal for Fiber Optic and Laser Applications
- 750 – 850nm and 1000 – 2000nm Wavelength Ranges
- 1000:1 Extinction Ratio

Common Specifications



Physical & Mechanical Properties

Thickness (mm):	2.00	Thickness Tolerance (mm):	±0.2
Parallelism (arcmin):	<4	Dimensional Tolerance (mm):	+0.0/-0.2
Construction:	Dichroic Polarizing Film on Glass		

Optical Properties

Extinction Ratio:	1000:1		
Substrate:	Polymer Film on B270	Transmission Tolerance (%):	±3

Technical Information



Products

Extinction Ratio	Wavelength Range (nm)	Dia. (mm)	Dimensional Tolerance (mm)	Thickness (mm)	Parallelism (arcmin)	Stock Number	Price	Buy
1000:1	750 - 850	12.50	+0.0/-0.2	2.00	<4	#48-891	₹23,199 Qty 6+ ₹19,930	10 to 12 days
1000:1	750 - 850	25.00	+0.0/-0.2	2.00	<4	#48-892	₹29,972 Qty 6+ ₹25,146	10 to 12 days
1000:1	750 - 850	30.00	+0.0/-0.2	2.00	<4	#48-893	₹29,972 Qty 6+ ₹25,457	10 to 12 days
1000:1	750 - 850	50.00	+0.0/-0.2	2.00	<4	#48-894	₹42,428 Qty 6+ ₹36,278	10 to 12 days
1000:1	1000 - 2000	12.50	+0.0/-0.2	2.00	<4	#48-887	₹23,199 Qty 6+ ₹19,930	10 to 12 days
1000:1	1000 - 2000	25.00	+0.0/-0.2	2.00	<4	#48-888	₹29,972 Qty 6+ ₹25,146	10 to 12 days
1000:1	1000 - 2000	30.00	+0.0/-0.2	2.00	<4	#48-889	₹29,972 Qty 6+ ₹25,457	10 to 12 days
1000:1	1000 - 2000	50.00	+0.0/-0.2	2.00	<4	#48-890	₹42,428 Qty 6+ ₹36,278	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
Phone: 1-800-363-1992 : www.edmundoptics.com