


[All Products](#) / [Optics](#) / [Polarization Optics](#) / [Linear Polarizers](#) / [Brewster Windows](#)

TECHSPEC® Brewster Windows




- Reduce Loss of P-Polarized Light
- Circular Profile When Oriented at 55.57°
- Great for Use in Laser Cavities

Common Specifications

Physical & Mechanical Properties			
Thickness (mm):	2.00 ±0.20	Edges:	Fine Ground
Parallelism (arcsec):	≤10	Young's Modulus (GPa):	73
Construction:	Brewster Window		
Optical Properties			
Coating:	Uncoated		
Design Wavelength DWL (nm):	632.8	Index of Refraction (n _d):	1.458
Substrate:	Fused Silica (Corning 7980)	Surface Quality:	10-5
Transmitted Wavefront, P-V:	λ/10	Wavelength Range (nm):	200 - 2200
Material Properties			
Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):	0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)		

Technical Information



Products

Thickness (mm)	Coating	Edges	Minor Axis (mm)	Substrate	Stock Number	Price	Buy
2.00	Uncoated	Fine Ground	10.00	Fused Silica	#65-823	₹6,308 Qty 11+ ₹5,685	10 to 12 days
2.00	Uncoated	Fine Ground	12.50	Fused Silica	#65-824	₹6,858 Qty 11+ ₹6,161	10 to 12 days
2.00	Uncoated	Fine Ground	25.00	Fused Silica	#65-827	₹9,169 Qty 11+ ₹8,215	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com