

[See all 16 Products in Family](#)

TECHSPEC[®] 0.16X SilverTL[™] Telecentric Lens



0.16X Magnification



Stock **#56-675** 3 In Stock

-

1

+

MRP ₹57,747

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹57,747 each
Need More?	Request Quote

Product Downloads

General	
SilverTL [™] Series	Product Family:
#56-871 Sold Separately	Stock No. of Mounting Clamp:
Telecentric Lens	Type:

Physical & Mechanical Properties	
Variable	Iris Option:
191.00	Length (mm):
191.00	Length excluding Threads (mm):
65.00	Maximum Diameter (mm):
416	Weight (g):
Anodized Aluminum	Construction:
Optical Properties	
40mm	Horizontal Field of View, 1/2" Sensor:
30mm	Horizontal Field of View, 1/3" Sensor:
8.00	Maximum Image Circle (mm):
0.008	Numerical Aperture NA, Object Side:
±3	Working Distance Tolerance (mm):
>40% @ 40 lp/mm	Resolution, Image Space MTF @ f/10:
8 (6)	Number of Elements (Groups):
<0.030	Typical Telecentricity @ 588nm (°):
<0.015	Typical Distortion @ 588nm (%):
0.16X	Primary Magnification PMAG:
0.16	Telecentric Lens Magnification:
177.00	Working Distance (mm):
40.0 x 30.0	FOV @ Max Sensor Format, H x V (mm):
f/6 - f/22	Aperture (f/#):
425 - 675nm BBAR	Coating:
±19.74 at f/10 (20% @ 20 lp/mm)	Depth of Field (mm):
0.16X	Magnification:
VIS	Lens Wavelength Range:
Sensor	
1/2"	Maximum Sensor Format:
2.74	Pixel Size (µm):
Threading & Mounting	
M62 x 0.75 (Female)	Filter Thread:
C-Mount	Mount:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:
China	Country of Origin:

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000


Product Details

- High Resolution f/6 Bi-Telecentric Lens with Inline Illumination Options
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Up to 2/3", C-Mount Telecentric Lens
- Magnification from 0.16X to 4X


TECHSPEC® SilverTL™ Telecentric Lenses are ideal for both on-line and off-line machine vision production applications that require accurate measurements. These lenses combine high-quality optics with a simplified non-focusing mechanical design and an adjustable iris with a locking set screw. These lenses are designed for metrology and gauging applications. TECHSPEC® SilverTL™ Telecentric Lenses also offer inline illumination options for maximum versatility. Each lens also features a standard front filter thread for use with [color filters](#), [polarizers](#), [protective windows](#), and [illumination adapters](#) for LED or fiber-optic ring lights.

Note: Mounting brackets are available that fit the 30mm diameter mounting surface.


Technical Information



#56-675, 0.16X SilverTL™ Telecentric Lens, Distortion Plot



#56-675, 0.16X SilverTL™ Telecentric Lens, Relative Illumination Plot




#56-675, 0.16X SilverTL™ Telecentric Lens, Telecentricity Plot



#56-675, 0.16X SilverTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 177mm Working Distance, f6



#56-675, 0.16X SilverTL™ Telecentric Lens, Depth of Field Plot, 177mm Working Distance, f6





#56-675, 0.16X SilverTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 177mm Working Distance, f10



#56-675, 0.16X SilverTL™ Telecentric Lens, Depth of Field Plot, 177mm Working Distance, f10

Stock Number	Primary Mag.	Max. Diameter A	Mounting Diameter B	Length C	Mounting Length D	Mounting Offset E	Filter Thread F
#56-675	0.16X	65mm	30mm	191mm	50mm	43mm	M62 x0.75
#63-073	0.20X	60mm	30mm	188mm	42mm	45mm	M58 x0.75
#56-676	0.25X	48mm	30mm	158mm	49mm	44mm	M46 x0.75
#58-428	0.30X	46mm	30mm	158mm	60mm	43mm	M43 x0.75
#56-677	0.40X	45mm	30mm	159mm	67mm	33mm	M43 x0.75
#63-074	0.50X	40mm	30mm	153mm	42mm	68mm	M37 x0.75
#88-344 (In-Line)	0.60X	42mm	30mm	156.2mm	45.1mm	73.4mm	M40.5 x0.5
#56-678				156mm	57mm	46mm	
#67-731				151.2mm	34mm*	82.2mm	
#88-346 (In-Line)	0.75X	36mm	30mm	155.2mm	46.2mm	16.9mm	M30.5 x0.5
#58-430	1.0X	40mm	30mm	114mm	32mm*	17mm	M37 x0.75
#58-431	2.0X	45mm	30mm	141mm	45mm	17mm	M43 x0.75
#88-348 (In-Line)	4.0X	61mm	30mm	144.6mm	42.2mm	18.8mm	M58 x0.75
#58-432				249mm	99mm	17mm	



*Mounting clamp fits over iris

