

[All Products](#) / [Optics](#) / [Polarization Optics](#) / [Linear Polarizers](#) / [Absorptive \(Dichroic\) Polarizers](#) / [Laminated Film Polarizers](#)

Broadband Polarizers




- Wide Acceptance Angles
- Broadband Performance from 300 -2700nm
- Compact Designs Ease System Integration

Common Specifications

Physical & Mechanical Properties			
Thickness (mm):	2.50 ±0.3	Dimensional Tolerance (mm):	+0.0/-0.1
Optical Properties			
Angle of Incidence (°):	±40	Wavelength Range (nm):	300 - 2700
Polarization Axis Mark (°):	±2		
Threading & Mounting			
Mount Thickness (mm):	4.5		
Environmental & Durability Factors			
Operating Temperature (°C):	-50 to 80		

Technical Information



Products

Extinction Ratio	Wavelength Range (nm)	Dia. (mm)	Dimensional Tolerance (mm)	Thickness (mm)	AOI (°)	Stock Number	Price	Buy
#71-207 New								
>100:1 @ 300 - 400nm (Typical) >50,000:1 @ 450 - 550nm (Typical) >800:1 @ 700 - 1400nm (Typical) >1000:1 @ 1400 - 2650nm (Typical)	300 - 2700	12.70	+0.0/-0.1	2.50	±40		₹58,388	10 to 12 days
						New		
						Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
>100:1 @ 300 - 400nm (Typical) >50,000:1 @ 450 - 550nm (Typical) >800:1 @ 700 - 1400nm (Typical) >1000:1 @ 1400 - 2650nm (Typical)	300 - 2700	25.40	+0.0/-0.1	2.50	±40	#89-602	₹83,689	10 to 12 days

[#71-208 New](#)



New

Launched
on our
website
before
appearing
in our
latest print
catalogs.
Be the
first to buy
before
anyone
else.

₹2,31,604

[Contact Us](#)

>100:1 @
300 -
400nm
(Typical)
>50,000:1
@ 450 -
550nm
(Typical)
>800:1 @
700 -
1400nm
(Typical)

300 - 2700

50.80

+0.0/-0.1

2.50

±40



Edmund
optics | worldwide

(Typical)
Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar,
Bengaluru, Karnataka, India 560038
Phone: 1-800-363-1992 :
www.edmundoptics.com
