

[All Products](#) / [Lasers](#) / [Laser Sources](#) / [Material Processing Lasers](#)

## Coherent® Diamond C-Series CO<sub>2</sub> Lasers See More by [Coherent®](#)



- Superior Beam Quality and Power Stability for Improved Process Quality
- Fully Sealed Integrated Package with Built-in RF Power Supply
- Wide Power Range with CW or Pulse Width Modulation Control



Common Specifications

General	
Cooling Method:	Air
Note: Max. Case Temperature: 60°C	
Laser Class - CDRH:	IV
Optical Properties	
Polarization:	>100:1
Wavelength (nm):	10,600.00
Color: Infrared	
Bandwidth (nm):	10,550 - 10,630
Electrical	
Operating Duty Cycle:	0 to 100% DC
Frequency (kHz):	0 to 100
Hardware & Interface Connectivity	
Power Supply:	Power Supply Required and Sold Separately: USA: <a href="#">#17-206</a> Europe: <a href="#">#17-206</a> Japan: <a href="#">#17-206</a> Korea: <a href="#">#</a> China: <a href="#">#17-206</a>
Output Type:	Free Space
Environmental & Durability Factors	
Operating Temperature (°C):	5 to 40
Storage Temperature (°C):	-10 to +60 Non-Condensing

**Technical Information**

# Products

Wavelength (nm)	Beam Diameter (mm)	Beam Divergence (mrad)	Polarization	Power Stability (%)	Output Power (W)	Stock Number	Price	Buy
10,600.00	1.8	7.5 ±0.5	>100:1	±8	20	<a href="#">#37-077</a>	₹3,51,000	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038  
Phone: 1-800-363-1992 : [www.edmundoptics.com](http://www.edmundoptics.com)