

**TECHSPEC® 0.184X, 2/3" C-Mount TitanTL® Telecentric Lens**



TitanTL® Telecentric Lens



Stock **#34-005** **2 In Stock**

1 MRP ₹1,74,320

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹1,74,320 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

TitanTL® Series **Product Family:**  
Telecentric Lens **Type:**

**Physical & Mechanical Properties**

Iris Option:

Variable	
145.50	Length (mm):
79	Maximum Diameter (mm):
0.74	Weight (kg):
25.4	Rear Filter Diameter (mm):

## Optical Properties

47.8mm	Horizontal Field of View, 2/3" Sensor:
39.1mm	Horizontal Field of View, 1/1.8" Sensor:
34.7mm	Horizontal Field of View, 1/2" Sensor:
11.00	Maximum Image Circle (mm):
0.0115	Numerical Aperture NA, Object Side:
70 lp/mm @ 36% (MTF, open)	Resolution, Image Space:
6 (4)	Number of Elements (Groups):
0.184X	Primary Magnification PMAG:
0.18	Telecentric Lens Magnification:
110	Working Distance (mm):
47.8 x 35.9	FOV @ Max Sensor Format, H x V (mm):
f/8 - f/22	Aperture (f/#):
M4 MgF <sub>2</sub>	Coating:
±11.5mm (20% @ 20 lp/mm, open)	Depth of Field (mm):
0.184X	Magnification:
70 lp/mm @ 36%	Resolution, Image Space MTF @ F8:
<0.05	Typical Distortion @ 520nm (%):
<0.1	Typical Telecentricity @ 520nm (°):
VIS	Lens Wavelength Range:

## Sensor

2/3"	Maximum Sensor Format:
2.74	Pixel Size (µm):

## Threading & Mounting

M72 x 0.75 (Female)	Filter Thread:
C-Mount	Mount:

## Regulatory Compliance

<a href="#">View</a>	Certificate of Conformance:
China	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

## Product Details


- Large Field of View Telecentric Lens
- Up to 31.4 MegaPixels, 3.45µm Pixel Size Sensors
- Full Frame (35mm), C-Mount, T-Mount, M58-Mount, F-Mount Telecentric Lens
- Magnification from 0.037X to 0.377X

TECHSPEC® TitanTL® Telecentric Lenses are designed for machine vision systems and metrology applications that require a large field of view. These lenses feature large maximum sensor formats, a variety of working distance and magnification options, and a rear filter holder on the back of the lenses to allow for easy filter integration. On our 118mm, 182mm and 242mm FOV versions, the integrated mounting flange allows for ease of securing each lens without requiring an additional mount and provides an easy to locate reference plane. TECHSPEC® TitanTL® Telecentric Lenses contain shims that provide adjustment for variation in camera sensor location, an adjustable iris and a 3 set screw lens mount for simple rotational alignment to the camera. Typical applications include automotive and electronic inspection, measurement and gauging applications.


These lenses won the [Silver Level 2017 Innovators Award](#).

**Note:** Detailed inspection reports included with each lens.


## Technical Information




#34-005, 0.184X, 2/3" C-Mount TitanTL® Telecentric Lens, Distortion Plot




#34-005, 0.184X, 2/3" C-Mount TitanTL® Telecentric Lens, Relative Illumination Plot




#34-005, 0.184X, 2/3" C-Mount TitanTL® Telecentric Lens, Telecentricity Plot




#34-005, 0.184X, 2/3" C-Mount TitanTL® Telecentric Lens, Modulated Transfer Function (MTF) Plot, 110mm Working Distance, f8



#34-005, 0.184X, 2/3" C-Mount TitanTL® Telecentric Lens, Depth of Field Plot, 110mm Working Distance, f8



#34-005, 0.184X, 2/3" C-Mount TitanTL® Telecentric Lens, Modulated Transfer Function (MTF) Plot, 110mm Working Distance, f10



#34-005, 0.184X, 2/3" C-Mount TitanTL® Telecentric Lens, Depth of Field Plot, 110mm Working Distance, f10