

0.19X, High Resolution Inline Telecentric Lens



Stock #65-026 10 TO 12 DAYS

- 1 +

₹368,880.00

ADD TO CART

Qty 1+
₹368,880.00

Volume Pricing
Request Quote

Get Product Downloads

Horizontal Field of View, 2/3" Sensor:
46.9mm

Numerical Aperture NA, Object Side:
0.017

Resolving Power, Image Space (µm):
4.00

Working Distance Tolerance (mm):
±3.00

Note:
Magnification Tolerance %: ±3

Type: Telecentric Lens
Primary Magnification PMAG: 0.19X
Maximum Sensor Format: 2/3"
Working Distance (mm): 110.00
Mount: C-Mount
Style: In-Line Illumination
Aperture (f/#): f/6
Distortion (%): ≤0.02
Compatible Light Guide/Source: 1/4" (0.312")
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View