


[All Products](#) / [Optics](#) / [Polarization Optics](#) / [Linear Polarizers](#) / [Absorptive \(Dichroic\) Polarizers](#) / [Polymer Film Polarizers](#)

High Contrast Near-Infrared (NIR) Polarizing Film



- >1,000:1 Extinction Ratio from 700nm-1600nm
- Ideal for NIR Imaging Applications
- Affordable Alternative to Conventional Glass Polarizers
- [Ultra-Broadband NIR Polarizing Films](#) also Available

Common Specifications

Physical & Mechanical Properties

Thickness (mm):	0.50 (Nominal)	Construction:	Polarizing Film
-----------------	----------------	---------------	-----------------

Optical Properties

Coating:	Uncoated	Extinction Ratio:	>1000:1 (700nm-1600nm) >10000:1 AVG (400nm-800nm)
Substrate:	Polymer Film on TAC	P-Polarization Transmission (%):	532nm: 65 830nm: 70 1550nm: 80
S-Polarization Transmission (%):	532nm: 0.002 830nm: 0.04 1550nm: 0.1	Surface Quality:	80-50
Wavelength Range (nm):	420 - 1600		

Environmental & Durability Factors

Cold Resistance (°C x Hours):	-40 x 500		
Environmental Durability:	DIN ISO 9022-2-10-07 DIN ISO 9022-2-11-05 DIN ISO 9022-2-12-07 DIN ISO 9022-2-14-05	Storage Temperature (°C):	15-25

Technical Information

Products

Dia. (mm)	Dimensions (mm)	Thickness (mm)	Stock Number	Price	Buy
10.00	-	0.50	#70-995	₹2,803 Qty 10+ ₹2,258	10 to 12 days
12.50	-	0.50	#70-996	₹3,348 Qty 10+ ₹2,647	10 to 12 days
-	12.5 x 12.5	0.50	#25-107	₹3,348 Qty 10+ ₹2,647	10 to 12 days
20.00	-	0.50	#70-997	₹6,072 Qty 10+ ₹4,827	7 days
25.00	-	0.50	#70-998	₹8,641 Qty 10+ ₹6,929	10 to 12 days
-	25.0 x 25.0	0.50	#25-106	₹8,641 Qty 10+ ₹6,929	Contact Us
50.00	-	0.50	#70-999	₹24,756 Qty 10+ ₹19,852	Contact Us
-	50.0 x 50.0	0.50	#25-105	₹24,756 Qty 10+ ₹19,852	Contact Us
-	76.0 x 76.0	0.50	#25-104	₹34,254 Qty 10+ ₹27,481	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com