

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Plano-Concave \(PCV\) Lenses](#)

ISP Optics Calcium Fluoride (CaF₂) Plano-Concave (PCV) Lenses

 See More by [ISP Optics](#)


- Low Index of Refraction
- IR Grade Calcium Fluoride Substrates
- Standard Imperial Sizes for Easy Benchtop Integration

Common Specifications

Physical & Mechanical Properties

Bevel:		Protective as needed	Centering (arcmin):		<3
Optical Properties					
Substrate:		Calcium Fluoride (CaF₂)	Coating:		Uncoated
Wavelength Range (nm):		300 - 8000	Focal Length Tolerance (%):		±2
Surface Quality:		60-40	Irregularity (P-V) @ 632.8nm:		λ

Technical Information

Products

Dia. (mm)	EFL (mm)	BFL (mm)	CT (mm)	Model Number	Stock Number	Price	Buy
#24-779 Clearance							
<div><div></div><div>×</div></div>							
Clearance							
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
12.70	- 50.80	-	1.50	CF-PC-12-50		₹12,150 Qty 10+ ₹10,935	10 to 12 days
#24-782 Clearance							
<div><div></div><div>×</div></div>							
Clearance							
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
25.40	- 63.50	-	2.00	CF-PC-25-63		₹13,950 Qty 10+ ₹12,555	10 to 12 days

[#24-785 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear.

Sorry, we cannot accept returns.

Receive up to 80% off select products.

38.10 - 63.50 - 2.50 CF-PC-38-63

₹28,350
Qty 10+ ₹25,515

10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com