

[See all 1 Products in Family](#)

## -18 to +18 diopters, VIS Coated, Manually Focus-Tunable Lens

See More by [Optotune](#)



Stock #12-329 **1 In Stock**

⊖ 1 ⊕ MRP ₹81,774

📌 Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹81,774 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Specialty Lens **Type:**

>100,000 **Lifecycles:**

ML-20-37 **Model Number:**

### Physical & Mechanical Properties

39.50 **Diameter (mm):**

20	<b>Clear Aperture CA (mm):</b>
18.60	<b>Thickness (mm):</b>
<b>Optical Properties</b>	
Low Dispersion Polymer	<b>Substrate:</b> <input type="checkbox"/>
BBAR (400-700nm)	<b>Coating:</b>
400 - 700	<b>Wavelength Range (nm):</b>
65	<b>Abbe Number (<math>v_d</math>):</b>
-18 to +18 diopter -55 to +55mm	<b>Focus Range (mm):</b>
1.38	<b>Index of Refraction (<math>n_d</math>):</b>
0.25 $\lambda$ @ 525nm	<b>Transmitted Wavefront Error, RMS:</b>
10 kW/cm <sup>2</sup> @ 1064nm	<b>Damage Threshold, By Design:</b> <input type="checkbox"/>

<b>Threading &amp; Mounting</b>	
C-Mount (Female)	<b>Mounting Threads:</b>

<b>Regulatory Compliance</b>	
<a href="#">View</a>	<b>Certificate of Conformance:</b>
Slovakia	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Manually Adjustable Focal Length
- Concave to Convex Convertible Lens Shape
- BBAR Coating for Increased Performance Across Wavelength Range

Optotune Manually Focus Tunable Lenses are designed to have their lens curvature change between convex, flat, and concave by the rotation of the outer adjustment ring. This allows for the focal length of the lens to be tuned to the precise value required for an optical application. The rotation mechanism is extremely durable, providing a lifecycle greater than 100,000 rotations. Optotune Manually Focus Tunable Lenses provide a simple, cost-effective solution for applications where system parameters are still being decided, such as in system prototyping or R&D applications. These focus tunable lenses can also be used singularly as an adjustable eye relief or as a pair to build a variable beam expander.