

TECHSPEC® 0.050X, 1/1.8" C-Mount TitanTL® Telecentric Lens



TitanTL® Telecentric Lens

Stock **#34-002** 10 TO 12 DAYS

⊖ 1 ⊕

₹345,608.00

ADD TO CART

Qty 1+
₹345,608.00
Volume Pricing
Request Quote

Get Product Downloads

Horizontal Field of View, 1/2" Sensor:
129.4mm

Weight (kg):
6.98

Numerical Aperture NA, Object Side:
0.0031

Resolution, Image Space:
70 lp/mm @40% (MTF, open)

Number of Elements (Groups):
6 (4)

Note: TitanTL®
Horizontal Field of View, 1/1.8" Sensor: 145.6mm
Type: Telecentric Lens
Primary Magnification PMAG: 0.050X
Maximum Sensor Format: 1/1.8"
Working Distance (mm): 287
Mount: C-Mount
Aperture (f/#): f/8 - f/16
Coating: λ/4 MgF ₂
Depth of Field (mm): ±159.4mm (20% @ 20 lp/mm, open)
FOV @ Max Sensor Format, H x V (mm): 144.0 x 108.0
Resolution, Image Space MTF @ F8: 70 lp/mm @ 40%
Rear Filter Diameter (mm): 12.7
Typical Distortion @ 520nm (%): <0.03
Typical Telecentricity @ 520nm (°): <0.1
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View