

[See all 19 Products in Family](#)

0.22 NA UV/VIS Patchcord 100 Micron Fiber w/ FC Connector



Stock **#23-705** **2 In Stock**

-

1

+

₹15,025

ADD TO CART

Volume Pricing	
Qty 1-4	₹15,025 each
Qty 5-10	₹13,546 each
Qty 11+	₹12,028 each
Need More?	Request Quote

Product Downloads

General

Patchcord	Type:
Multimode	Fiber Cable Type:

Physical & Mechanical Properties

1.5	Length (m):
-----	-------------

100	Core Diameter (µm):
PVC MONOCOIL (0.112" OD)	Jacket Material:
Optical Properties	
Nylon	Coating Type:
0.22	Numerical Aperture NA:
UV-VIS	Wavelength:
Hardware & Interface Connectivity	
FC/PC	Connector:
Environmental & Durability Factors	
-40 to +100	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:
Canada	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- UV/VIS and VIS/NIR Versions Available
- FC Connector Compatible with [Spatial Filters](#)
- FC Connector Compatible with [Fiber Alignment Mounts](#)
- FC and SMA Connector Options

High Quality Fiber Patchcords are designed for UV-VIS (190 - 1250nm) or VIS-NIR (300 - 2400nm) ranges. These Patchcords are 1.5 meters in length with Nylon or Tefzel coatings. With core diameters ranging from 50 – 1000µm, these patchcords provide quality solutions for a variety of core sizes. High Quality Fiber Patchcords are available with SMA905 or FC/PC connectors featuring a 0.22 numerical aperture. These Patchcords are ideal for applications requiring optimum transmission in the UV-VIS or VIS-IR wavelengths.

Technical Information

