

[See all 2 Products in Family](#)

0.1 OD, 25.4mm Dia., Reflective Neutral Density Filter



Stock #27-926 CLEARANCE **4 In Stock**

MRP ₹1,610

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹1,610 each
Need More?	Request Quote

Product Downloads

General

Neutral Density Filter **Type:**

Physical & Mechanical Properties

25.40 ±0.3 **Diameter (mm):**

1.00 ±0.25 **Thickness (mm):**

±3 **Parallelism (arcmin):**

±0.3	Dimensional Tolerance (mm):
>90	Clear Aperture (%):
Optical Properties	
0.1	Optical Density OD (Average):
Borosilicate	Substrate: <input type="checkbox"/>
Metallic Based ND	Coating:
79.00	Transmission (%):
±10	Optical Density Tolerance (%):

Regulatory Compliance

View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Feature Standard Designs and Specifications
- Constant Density Values Across the Surface
- For More Options, View Precision Quality [Reflective Neutral Density Filters](#)

Neutral density filters have constant density values across the surface. In stacks, the total density is the sum of each filter's density. Neutral density filters are primarily used for the attenuation of light over a wide spectral range. They are often used in laser and photometer applications, where excessive power can cause damage or inaccurate results. Commercial Grade Reflective Neutral Density Filters offer commercial quality, at an affordable price.

Note: Orient the mirrored side toward the source at an angle of incidence of 0°.