

[See all 4 Products in Family](#)

0.26 NA, 11.0mm FL, RPO VIS Molded Glass Aspheric Lens



Stock **#73-654** 20+ In Stock

-

1

+

₹7,395

ADD TO CART

Volume Pricing	
Qty 1+	₹7,395 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens

Type:

Physical & Mechanical Properties

7.20 ±0.015

Diameter (mm):

5.50

Clear Aperture CA (mm):

5.00

Center Thickness CT (mm):

Bevel:

Protective as needed	
Optical Properties	
11.00	Effective Focal Length EFL (mm):
0.26	Numerical Aperture NA:
D-K59	Substrate: □
633	Aspheric Design Wavelength (nm):
BBAR (400 - 600nm)	Coating:
R _{avg} <1% @ 400 - 600nm	Coating Specification:
60-40	Surface Quality:
1.53	f/#:
400 - 600	Wavelength Range (nm):
7.97	Working Distance (mm):

Regulatory Compliance	
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Precision Visible Glass Molded Lenses
- Ideal for High Volume Production Requirements
- Multiple Glass Substrates Available

Rochester Precision Optics (RPO) Visible Molded Glass Aspheric Lenses offer several key benefits, including high precision, >99% transmission, and improved performance by reducing optical aberrations, leading to smaller spot sizes and sharper images. Cost-effective molding processes enable options for high-quantity OEM integration while maintaining consistent specifications. Rochester Precision Optics (RPO) Visible Molded Glass Aspheric Lenses are available with various focal lengths and numerical apertures and are AR coated for >99% transmission from 400 - 600nm. Their lightweight form factor, small diameter, and reduced thickness allow these molded aspheric lenses to be integrated into cameras, aerospace systems, measurement systems, biomedical instrumentation, and handheld optical tools.