

TECHSPEC® 0.28X, 2/3" C-Mount PlatinumTL™ Telecentric Lens



0.28X Magnification, #62-933

Stock **#62-933** 10 TO 12 DAYS

- 1 +

₹132,762.00

ADD TO CART

Qty 1+
₹132,762.00

Volume Pricing
Request Quote

Get Product Downloads

Length (mm):
203.80

Horizontal Field of View, 1/2" Sensor:
22.9mm

Horizontal Field of View, 2/3" Sensor:
31.8mm

Filter Thread:
M58 x0.75 (Female)

Maximum Diameter (mm):
60.5

Weight (g): 736
Numerical Aperture NA, Object Side: 0.023
Stock No. of Mounting Clamp: #63-442 Sold Separately
Flange Distance (mm): 17.5
Number of Elements (Groups): 10 (7)
Typical Telecentricity @ 588nm (°): <0.030
Typical Distortion @ 588nm (%): <0.006
Type: Telecentric Lens
Primary Magnification PMAG: 0.28X
Maximum Sensor Format: 2/3"
Working Distance (mm): 180.00
Mount: C-Mount
Aperture (f/#): f/6 - f/22
Coating: 425 - 675nm BBAR
Depth of Field (mm): ±6.9mm at f/10 (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 31.4 x 23.6
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View