

TECHSPEC[®] 0.28X, 28.7mm F-Mount PlatinumTL[™] Telecentric Lens



0.28X Magnification

Stock #62-922 2 In Stock

-

1

+

₹3,38,605

ADD TO CART

Volume Pricing	
Qty 1+	₹3,38,605 each
Need More?	Request Quote

Product Downloads

General

PlatinumTL[™] Series

Series:

[#63-440](#) Sold Separately

Stock No. of Mounting Clamp:

Telecentric Lens

Type:

Physical & Mechanical Properties

Variable

Iris Option:

167.60	Length (mm):
138.6	Maximum Diameter (mm):
736	Weight (g):

46.5	Flange Distance (mm):
------	-----------------------

Optical Properties

80.0mm	Horizontal Field of View, APS-C Sensor:
--------	---

102.5mm	Field of View, 28.7mm Sensor:
---------	-------------------------------

61.8mm	Horizontal Field of View, 4/3" Sensor:
--------	--

50.7mm	Horizontal Field of View, 1.1" Sensor:
--------	--

45.7mm	Horizontal Field of View, 1" Sensor:
--------	--------------------------------------

31.8mm	Horizontal Field of View, 2/3" Sensor:
--------	--

22.9mm	Horizontal Field of View, 1/2" Sensor:
--------	--

28.70	Maximum Image Circle (mm):
-------	----------------------------

0.023	Numerical Aperture NA, Object Side:
-------	-------------------------------------

10 (7)	Number of Elements (Groups):
--------	------------------------------

<0.035	Typical Telecentricity @ 588nm (°):
--------	-------------------------------------

<0.012	Typical Distortion @ 588nm (%):
--------	---------------------------------

0.28X	Primary Magnification PMAG:
-------	-----------------------------

0.28	Telecentric Lens Magnification:
------	---------------------------------

182.00	Working Distance (mm):
--------	------------------------

80.0 x 60.0	FOV @ Max Sensor Format, H x V (mm):
-------------	--------------------------------------

f/6 - f/22	Aperture (f/#):
------------	-----------------

425 - 675nm BBAR	Coating:
------------------	----------

±6.9 at f/10 (20% @ 20 lp/mm)	Depth of Field (mm):
-------------------------------	----------------------

0.28X	Magnification:
-------	----------------

VIS	Lens Wavelength Range:
-----	------------------------

Sensor

APS-C	Maximum Sensor Format:
-------	------------------------

2.74	Pixel Size (µm):
------	------------------

Threading & Mounting

M132 x 0.75 (Female)	Filter Thread:
----------------------	----------------

F-Mount	Mount:
---------	--------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

China	Country of Origin:
-------	--------------------


Edmund Optics India Private Limited	Imported By:
-------------------------------------	--------------

Product Details


- High Resolution f/6 Bi-Telecentric Lens for Measurement
- Up to 35 MegaPixels, 2.8µm Pixel Size Sensors
- APS-C, C-Mount, T-Mount, F-Mount Telecentric Lens
- Magnification from 0.28X to 1.7X

TECHSPEC® PlatinumTL™ Telecentric Lenses are designed for semiconductor and electronics inspection, measurement, and gauging applications. The precision designs feature high telecentricity (<0.1°), low distortion (<0.1%), and high light throughput with an adjustable aperture that achieves f/6 when fully open. Capable of supporting large format 28.7mm diagonal sensors, these lenses are compatible with the Sony IMX342 APS-C sensor and other similar format sensors such as the Sony IMX530. TECHSPEC® PlatinumTL™ Telecentric Lenses produce unparalleled levels of contrast yielding maximum image quality with the highest degree of measurement accuracy. These lenses are suitable for high vibration environments and feature a removable recessed set screw for securing the iris in place.


Technical Information




#62-922, 0.28X, 28.7mm F-Mount PlatinumTL™ Telecentric Lens, Distortion Plot




#62-922, 0.28X, 28.7mm F-Mount PlatinumTL™ Telecentric Lens, Relative Illumination Plot




#62-922, 0.28X, 28.7mm F-Mount PlatinumTL™ Telecentric Lens, Telecentricity Plot



#62-922, 0.28X, 28.7mm F-Mount PlatinumTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 182mm Working Distance, f6



#62-922, 0.28X, 28.7mm F-Mount PlatinumTL™ Telecentric Lens, Depth of Field Plot, 182mm Working Distance, f6



#62-922, 0.28X, 28.7mm F-Mount PlatinumTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 182mm Working Distance, f10



#62-922, 0.28X, 28.7mm F-Mount PlatinumTL™ Telecentric Lens, Depth of Field Plot, 182mm Working Distance, f10

Description		Stock No.	Flange	Length (A)	Front Diameter (B)	Back Diameter (C)
0.28X	C-Mount	#62-933	17.5mm	230.8mm	60.5mm	33.5mm
0.5X	C-Mount	#62-932	17.5mm	174.9mm	50mm	33.5mm
1.7X	C-Mount	#63-232	17.5mm	189.5mm	60mm	46mm
0.28X	F-Mount	#62-922	46.5mm	167.6mm	138.6mm	55mm
	M42 x 1.0	#62-923	6.56mm	208.5mm	138.6mm	50mm
	M42 x 1.0	#62-924	19.53mm	195.5mm	138.6mm	50mm
0.5X	F-Mount	#62-912	46.5mm	143mm	90mm	55mm
	M42 x 1.0	#62-913	6.56mm	184mm	90mm	50mm
	M42 x 1.0	#62-914	19.53mm	171.1mm	90mm	50mm
0.9X	F-Mount	#62-902	46.5mm	170.8mm	65mm	55mm
	M42 x 1.0	#62-903	6.56mm	210.7mm	65mm	53mm
	M42 x 1.0	#62-904	19.53mm	197.8mm	65mm	53mm

