

[See all 8 Products in Family](#)

0.19 - 20μm, 3.8J, Pyroelectric Energy Detector



0.19 - 20μm, 3.8J, Pyroelectric Energy Detector

Stock **#78-468** NEW **1 In Stock**

-

1

+

₹1,90,095

ADD TO CART

Volume Pricing	
Qty 1+	₹1,90,095 each
Need More?	Request Quote

Product Downloads

Maximum Incident Energy Density (J/cm², 10ns Pulses):
0.6

General	
QE25LP-S-MB-INT-D0	Model Number:
Convection	Cooling Method:

1 of #15-267 is included	Note:
Maximum Incident Energy (J):	

3.8	
Integra (Integrated)	Compatible Meters:
Physical & Mechanical Properties	
50 x50 x 14	Dimensions (mm):
120	Weight (g):
0.12	Weight (kg):
25 x25	Active Area (mm):
Optical Properties	
190 - 20000	Wavelength Range (nm):
0.19 - 20	Wavelength Range (µm):
Sensor	
Pyroelectric	Type of Sensor:
Electrical	
5,000	Maximum Incident Beam Power (mW):
5	Maximum Incident Beam Power (W):
4 µJ	Noise Level:
Regulatory Compliance	
View	Certificate of Conformance:
Canada	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Photodetectors, Thermopiles, and Pyroelectric Detectors Available
- Various Active Area Sizes Across a Wide Range of Sensitivities
- [Meterless](#) and [Wireless](#) Detectors Also Available

Gentec-EO Integra USB Power and Energy Detectors combine a power meter and detector in one convenient package while providing fast response times and accurate measurements for beam analysis. These detectors are designed with a USB connector for easy connection to a PC or other acquisition system and include user-friendly software allowing for control via PC or serial commands. Versatile pyroelectric energy detectors with broadband coatings are optimized for low to high power densities. Gentec-EO Integra USB Power and Energy Detectors can be used with a variety of laser powers ranging from the nanowatts to multi-kilowatts. These detectors are ideal for laser energy measurement, thermal imaging, and remote sensing applications.