

[See all 76 Products in Family](#)

LightPath 355397 | 7.2mm Dia., 0.30 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-121** **16 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ MRP ₹7,567

📌 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹7,567 each
Qty 11-49	₹6,810 each
Need More?	Request Quote

Product Downloads

General

Thickness: 0.28 (t) (mm)
Material: BK7

Compatible Window:

355397

Lightpath Lens Code:

Aspheric Lens

Type:

Typical Applications:
Collimate or Focus Laser Light

Physical & Mechanical Properties

Diameter (mm):
7.20 ±0.020

Clear Aperture CA (mm):
6.68

Edge Thickness ET (mm):
1.28

Center Thickness CT (mm):
1.95 ±0.05

Bevel:
Protective as needed

Distance from Window to Lens (D) (mm):
9.346

Optical Properties

Effective Focal Length EFL (mm):
11.00 @670nm

Numerical Aperture NA:
0.30

Substrate:
[D-ZLaF52LA](#)

Focal Length Tolerance (%):
±1

Aspheric Design Wavelength (nm):
670

Coating:
BBAR (350-700nm)

Coating Specification:
R_{avg} ≤0.5% @ 350 - 700nm

Surface Quality:
60-40

f#:
1.67

Abbe Number (v_d):
40.79

Index of Refraction (n_d):
1.806

Wavelength Range (nm):
350 - 700

Working Distance (mm):
10

Conjugate Distance:
Infinite

Focal Length Specification Wavelength (nm):
670.00

Transmitted Wavefront Error (λ, RMS):
< 0.09

Material Properties

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
6.9

Environmental & Durability Factors

Operating Temperature (°C):
≤200

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 247:
[Compliant](#)

Country of Origin:
China

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information

