

[See all 77 Products in Family](#)

LightPath 355375 | 6.51mm Dia., 0.30 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-130** [CONTACT US](#)

☐ [Other Coating Options](#)

-

1

+

₹6,075

ADD TO CART

Volume Pricing	
Qty 1-10	₹6,075 each
Qty 11-49	₹5,400 each
Need More?	Request Quote

Product Downloads


General	
Thickness: 0.250 (t) (mm) Material: BK7	Compatible Window:
355375	Lightpath Lens Code:
Aspheric Lens	Type:

Typical Applications: Collimate or Focus Laser Light	
Physical & Mechanical Properties	
Diameter (mm):	6.51 ±0.020
Clear Aperture CA (mm):	4.54
Edge Thickness ET (mm):	2.71
Center Thickness CT (mm):	3.19 ±0.04
Bevel:	Protective as needed
Distance from Window to Lens (D) (mm):	5.151
Optical Properties	
Effective Focal Length EFL (mm):	7.50 @ 780nm
Numerical Aperture NA:	0.30
Substrate: □	D-ZLaF52LA
Focal Length Tolerance (%):	±1
Aspheric Design Wavelength (nm):	780
Coating:	BBAR (600-1050nm)
Coating Specification:	R _{abs} <1.0% @ 600 - 1050nm
Surface Quality:	40-20
f/#:	1.67
Wavelength Range (nm):	600 - 1050
Working Distance (mm):	5.8
Conjugate Distance:	Infinite
Transmitted Wavefront Error (λ, RMS):	< 0.05
Environmental & Durability Factors	
Operating Temperature (°C):	≤200
Regulatory Compliance	
RoHS 2015:	Compliant
Certificate of Conformance:	View
Reach 247:	Compliant
Country of Origin:	China
Imported By:	Edmund Optics India Private Limited


Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information



;